ASUS ROG RYUJIN III 240 ARGB White Edition Processor Alles-in-één vloeistofkoeler 12 cm Wit 1 stuk(s)

Merk : ASUS

Artikelcode: 90RC00K2-M0UAY0

Productnaam : ROG RYUJIN III 240 ARGB White Edition

ASUS ROG RYUJIN III 240 ARGB White Edition. Soort: Alles-in-één vloeistofkoeler, Ventilator diameter: 12 cm, Maximum luchtstroom: 70,07 cfm. Kleur van het product: Wit

Prestatie	
Geschikte locatie *	Processor
Soort *	Alles-in-één vloeistofkoeler
Ventilator diameter	12 cm
Supported processor sockets	LGA 1150 (Socket H3), LGA 1151 (Socket H4), LGA 1155 (Socket H2), LGA 1156 (Socket H), LGA 1200 (Socket H5), LGA 1700, Socket AM4, Socket AM5
Minimum luchtstroom	21,08 cfm
Maximum luchtstroom	70,07 cfm
Pulsbreedtemodulatie-ondersteuning	✓
Geluidsniveau ventilatie (max)	36,45 dB
Aantal per verpakking	1 stuk(s)
Pomp motor snelheid (min)	800 RPM
Pomp motor snelheid (max)	3600 RPM
Fan snelheid (min)	600 RPM
Fan snelheid (max)	2200 RPM
Statische druk ventilator	3,88 mmH2O

Design	
Kleur van het product *	Wit
Radiator materiaal	Aluminium
Basis plaat materiaal	Koper
Aantal ventilatoren	2 ventilator(en)
Aantal ventilatorbladen	9
Aantal warmte pijpen	2
Verlichtings-led	✓

Design	
Kleur van de verlichting	Multi
Waterblok materiaal	Koper
Type beeldscherm	LCD

Gewicht en omvang	
Radiator breedte	27,9 cm
Radiator diepte	12 cm
Radiator hoogte	3 cm
Buis lengte	40 cm
Breedte waterblok	8,9 cm
Diepte waterblok	9,1 cm
Hoogte waterblok	10,1 cm
Gewicht	1,4 kg
Maten ventilator (b x d x h)	120 x 120 x 25 mm
Ventilator 2 afmetingen (BxDxH)	120 x 120 x 25 mm
Breedte verpakking	307 mm
Diepte verpakking	241 mm
Hoogte verpakking	135 mm
Gewicht verpakking	2,56 kg

Technische details	
Garantieperiode	6 jaar

Inhoud van de verpakking	
Montage gereedschap	✓
Inclusief schroeven	✓
Installatie instructie	✓

4711387189375

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 09-JUN-2024. Prints or copies of Information are only valid on the printed Publication date